

EC DECLARATION OF CONFORMITY
The Pressure Equipment Directive 97/23/EC

Name and Address of Manufacturer within the European Community

Danfoss A/S
Albuen 29
DK 6000 Kolding
Denmark

Description of Pressure Equipment

Refrigerant check valve, with straight housing
Type **NRVA**

Nominal bore	DN32-65 mm. (1¼ - 2½ in.)	
Classified for	Fluid Group I (all refrigerants (toxic, non-toxic, flammable and non-flammable))	
Maximum allowable working pressure and temperature range	Standard applications	40 bar (580 psi) at -50°C/+140°C (-58°F/+284°F)

Conformity and Assessment Procedure Followed

Category	II
Module	D1
Certificate ID	07 202 1321 Z 0045/0/01
Nominal bore	DN32-65 mm. (1¼ - 2½ in.)

Name and Address of the Notified Body monitoring the Manufacturer's Quality Assurance System and carried out the Inspection

TÜV-NORD Systems GmbH & Co. KG.
Grosse Bahnstrasse 31
22525 Hamburg, Germany



References of Harmonised Standards used


EN 10028-3 EN 10213-3 EN 12284

References of other Technical Standards and Specifications used

Issued by:

Title: Director, Product & Application Support

Name: Niels P Vestergaard

Signature: 

Date: 30/01/2013

Approved by

Title: Sr. Director Supply Chain

Name: Karsten Jaeger

Signature: 

Date: 30/01/2013

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation