




EC DECLARATION OF CONFORMITY
The Pressure Equipment Directive 97/23/EC

Name and Address of Manufacturer within the European Community		
Danfoss A/S Albuen 29 DK 6000 Kolding Denmark		
Description of Pressure Equipment		
Refrigerant safety valve Type SFA 15, SFV 20 and 25		
Nominal bore	13 mm. (0,512 in.) for SFA 15 18 mm. (0,709 in.) for SFV 20 23 mm. (0,906 in.) for SFV 25	
Classified for	Fluid Group I (all refrigerants (toxic, non-toxic, flammable and non-flammable)) For further details / restrictions - see Installation Instruction	
Maximum allowable working pressure and temperature range	SFA 15	10-40 bar (143-580 psi) -50°C/+100°C (-58/+212°F)
	SFV 20-25	10-25 bar (143-362 psi) -50°C/+100°C (-58/+212°F)
Conformity and Assessment Procedure Followed		
Category	IV	
Module	B+D	
Certificate ID	B:	07 202 0511 Z 0078/1/H-0001
	D:	07 202 1321 Z 0045/0/01
Nominal bore	13 mm. (0,512 in.) for SFA 15	
	18 mm. (0,709 in.) for SFV 20	
	23 mm. (0,906 in.) for SFV 25	
Name and Address of the Notified Body monitoring the Manufacturer's Quality Assurance System and carried out the Inspection		
TÜV-NORD Systems GmbH & Co. KG. Grosse Bahnstrasse 31 22525 Hamburg, Germany		 (0045)
References of Harmonised Standards used		
EN 10213-3 EN 12284	EN 10222-4	EN 13136
References of other Technical Standards and Specifications used		
AD-Merkblätter		

Issued by: Title: Director, Product & Application Support Name: Niels P Vestergaard Signature:  Date: 30/01/2013	Approved by Title: Sr. Director Supply Chain Name: Karsten Jaeger Signature:  Date: 30/01/2013
--	---

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation