

**EC DECLARATION OF CONFORMITY**  
The Pressure Equipment Directive 97/23/EC

**Name and Address of Manufacturer within the European Community**

Danfoss A/S  
Albuen 29  
DK 6000 Kolding  
Denmark

**Description of Pressure Equipment**

Pilot operated internal safety valve  
**Type POV 600, 1050 and 2150**

Nominal bore	<b>DN40-80 mm.</b> (1½ - 3 in.)	
Classified for	<b>Fluid Group I</b> (all refrigerants (toxic, non-toxic, flammable and non-flammable)) For further details / restrictions - se Installation Instruction	
Restrictions	POV 600, 1050 and 2150	Only for use in conjunction with BSV 8.
Maximum allowable working pressure and temperature range	POV 600, 1050 and 2150	40 bar (580 psi) -50°C/+150°C (-58°F/+302°F)

**Conformity and Assessment Procedure Followed**

Category	<b>II</b>	
Module	<b>D1</b>	
Certificate ID	D1: 07 202 1321 Z 0045/0/01	
Nominal bore	DN40-80 mm. (1½ - 3 in.)	

**Name and Address of the Notified Body monitoring the Manufacturer's Quality Assurance System, and carried out the inspection**

TÜV-NORD Systems GmbH & Co. KG.  
Grosse Bahnstrasse 31  
22525 Hamburg, Germany



**References of Harmonised Standards used**

EN10213-3                                      EN10222-4                                      EN13136  
EN 12284

**References of other Technical Standards and Specifications used**

*Issued by:*  
**Title:** Director, Product & Application Support  
**Name:** Niels P Vestergaard  
**Signature:**   
**Date:** 30/01/2013

*Approved by*  
**Title:** Sr. Director Supply Chain  
**Name:** Karsten Jaeger  
**Signature:**   
**Date:** 30/01/2013