

EC DECLARATION OF CONFORMITY
The Pressure Equipment Directive 97/23/EC

Name and Address of Manufacturer within the European Community

Danfoss A/S
Albuen 29
DK 6000 Kolding
Denmark

Description of Pressure Equipment

Refrigerant change over valve
DSV

Nominal bore	DN 32 mm. (1¼ in.)	
Classified for	Fluid Group I (all refrigerants (toxic, non-toxic, flammable and non-flammable)) For further details / restrictions - see Installation Instruction	
Maximum allowable working pressure and temperature range	Standard application	PS40 bar (580 psi) at -50°C/+100°C (-58°F/+212°F)
Restrictions	Could only be used in systems in conjunction with two SFA15, SFV20 or SFV25 (Max. 3% pressure drop in upstream line according to prEN13136)	

Conformity and Assessment Procedure Followed

Category	II
Module	D1
Certificate ID	D1:07 202 1321 Z 0045/0/01
Nominal bore	DN 32 mm. (1¼ in.)

Name and Address of the Notified Body monitoring the Manufacturer's Quality Assurance System and carried out the Inspection

TÜV-NORD Systems GmbH & Co. KG.
Grosse Bahnstrasse 31
22525 Hamburg, Germany



References of Harmonised Standards used

EN 10028-3 EN 10213-3 EN 10222-4
EN 12284

References of other Technical Standards and Specifications used

Issued by:
Title: Director, Product & Application Support
Name: Niels P Vestergaard
Signature: _____
Date: 30/01/2013

Approved by
Title: Sr. Director Supply Chain
Name: Karsten Jaeger
Signature: _____
Date: 30/01/2013

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation