

## MANUFACTOR DECLARATION

### Name and Address of Manufacturer within the European Community

Danfoss A/S  
Albuen 29  
DK 6000 Kolding  
Denmark

### Declaration

We hereby declare that below mentioned equipment are Classified for Fluid Group II (non-toxic and non-flammable refrigerants), and that all are covered by Article 3, paragraph 3 of The Pressure Equipment Directive 97/23/EC.

### Description of Pressure Equipment

Electrically operated modulating control valves

#### Type CCM

<b>Classified for</b>	<b>Fluid group II (non-toxic and non-flammable refrigerants)</b>
Temperature range	-40°C/ +60°C (-40°F/+140°F)
Max. working pressure	90 barg (1305 psig)

#### Type CCMT

<b>Classified for</b>	<b>Fluid group II (non-toxic and non-flammable refrigerants)</b>
Temperature range	-40°C/ +60°C (-40°F/+140°F)
Max. working pressure	140 barg (2030 psig)

### Compliance with EU Directive 2002/95/EC (RoHS)

This product confirms to the restriction of the use of lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB), and polybrominated diphenyl ethers (PBDE) as described in Directive 2002/95/EC of January 2003 with the amendments in Commission Decision 2005/618/EC of 18 August 2005.


### References to Technical Standards and Specifications used

EN 12284

*Issued by:*

**Title:** Director, Product & Application Support

**Name:** Niels P Vestergaard


**Signature:** 

**Date:** 30/01/2013

*Approved by*

**Title:** Sr. Director Supply Chain

**Name:** Karsten Jaeger

**Signature:** 

**Date:** 30/01/2013

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation