

EC DECLARATION OF CONFORMITY
The Pressure Equipment Directive 97/23/EC

Name and Address of Manufacturer within the European Community

Danfoss A/S
Albuen 29
DK 6000 Kolding
Denmark

Description of Pressure Equipment

Refrigerant regulation valve, with straight bonnet arrangement

Type ICV PM

Nominal bore	DN 32-65 mm (1 1/4 - 2 1/2 in.)	
Classified for	Fluid Group I (all refrigerants (toxic, non-toxic, flammable and non-flammable)) For further details / restrictions - see Installation Instruction	
Maximum allowable working pressure and temperature range	Standard applications (DN 32-65)	28* bar (406 psi) -60°C/+120°C (-76°F/+248°F)

* Actual pressure marked on the valve

Conformity and Assessment Procedure Followed

	ICV PM
Category	II
Module	D1/D
Certificate ID	1321 P 0033/13/D/01
Nominal bore	ICV PM DN 32-65 mm (1 1/4 - 2 1/2 in.)

Name and Address of the Notified Body monitoring the Manufacturer's Quality Assurance System and carried out the Inspection

TÜV-NORD Systems GmbH & Co. KG.
Grosse Bahnstrasse 31
22525 Hamburg, Germany



References of Harmonised Standards used

EN 10213-3 EN 10222-4 EN 12284

References of other Technical Standards and Specifications used

Issued by:		Approved by:	
Title:	Design and Approval Expert	Title:	Senior Director R&D and Engineering
Name:	Claus Juhl	Name:	Henning Hansen
Signature:		Signature:	
Date:	09/02/2015	Date:	09/02/2015

Danfoss A/S only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator consumed shall be liable for the correctness of the translation