


Installation guide

ELIMINATOR® Hermetic bi-flow filter drier

Types DMB and DCB

023R9532

Refrigerants: R134a, R404A, R407C, R507, R22, R410A and other refrigerants (HCFC, HFC, HFO, HC)	Temperature range:  -40 – 70 °C -40 – 160 °F	Max. working pressure: PS / MWP = 46 bar / 667 psig
---	--	---

023R9532

