

Installation Guide

Check valve for high pressure

Type NRV 10s H



020R9504

020R9504

Refrigerant: R744 (CO₂)	Media temperature: T_{min}: -50 °C (-58 °F) T_{max}: 140 °C (285 °F)	Max. working pressure: PS/MWP = 90 bar (1305 psig)
---	---	---



When the NRV is used together with GBC in parallel as a pressure relief valve, it is recommended to install the NRV above the GBC.

