

## Instructions for downloading with the Danfoss code number as the search term:

Go to [www.danfoss.com](http://www.danfoss.com) or select a website in your own language here

Left-click in the "Product finder" search field and type the Danfoss code number (e.g. 148B3108)

Left-click the "Product specifications" search result

Left-click here

**148B3108**  
Refrigerants: all common refrigerants, incl. R 717 (NH<sub>3</sub>), non-corrosive gases/liquids. Temperature range: -60 - +150°C. Max. working pressure = 40 bar g. Fluid Group 1. Category: see code no.

Characteristic	Value
Type	SVA-HS 100
Weight	15.000 Kg
Approval	CE
Category	II
Colour paint	BLACK

Left-click here

Left-click the format you want to download

**Danfoss Group Global**

Product Finder

Refrigeration & Air Conditioning

148B3108

Choose size

- x-pt (203 KB dwg)
- x-pt (218 KB dxf)
- x-pt (263 KB iges)
- x-pt (80 KB sat)
- x-pt (116 KB stp)
- 152 x 115px (6 KB jpg)
- 640 x 480px (41 KB jpg)
- 1672 x 987px (45 KB jpg)

148B3108

Refrigerants: all common refrigerants, incl. R 717 (NH<sub>3</sub>), non-corrosive gases/liquids. Temperature range: -60 - +150°C. Max. working pressure = 40 bar g. Fluid Group 1. Category: see code no.

Product specifications | Code number selector

CAD Symbols (1) | Product labels (2)

Right-click here

Left-click here and save the file

**Danfoss Group Global**

Product Finder

Refrigeration & Air Conditioning

148B3108

Refrigerants: all common refrigerants, incl. R 717 (NH<sub>3</sub>), non-corrosive gases/liquids. Temperature range: -60 - +150°C. Max. working pressure = 40 bar g. Fluid Group 1. Category: see code no.

Product specifications | Code number selector

CAD Symbols (1) | Product labels (2)

Photos / Drawings - W...

Right-click to save 148B3108.dwg

- Open
- Open in New Tab
- Open in New Window
- Save Target As...
- Print Target