



REFRIGERATION AND
AIR CONDITIONING

INSTRUCTIONS

EKA 163A / 164A



084R9970



R18KB700

084R9970

084R9970

EKA 163A Universal display (084B8562)

EKA 164A Universal setting display (084B8563)

min. 8
29⁺¹₀
71⁺¹₀
min. 15

84
14
71

36
29

$t_{amb} = 0 - +55^{\circ}\text{C}$
Non condensing

$t_{amb} = -20 - +55^{\circ}\text{C}$
Non condensing



EKA 163A / EKA 164A → EKC 4xx / EKC 5xx / AK..

L = max. 15 m

(2 m: 084B7298)
(6 m: 084B7299)

Brun, Brown, Braun, Brun
Grøn, Green, Grün, Vert
Hvid, White, Weiss, Blanc

EKA 163A → EKC 202D / 204A1, AK-CC 210 / 260

L = max. 1000 m

Address, o03 > 0

Data communication: See literature RC8AC

EKC 202D, EKC 204A1, AK-CC 210

EKA 163A / 164A → AK-CC 450 / 550

L = max. 1000 m

Address, o03 > 0

Data communication: See literature RC8AC

AK-CC 450/550

EKA 164A → EKD 316

L = max. 1000 m

Address, o03 > 0

Data communication: See literature RC8AC

R=120 Ω
EKD 316