

037C3055

037C3055

Minicontactor CI 5-



Vigtig: Før monterings- eller servicearbejde, afbryd strømforsyning for at undgå ulykker.

Attention: To prevent electrical shock, disconnect from power source before installing or servicing.

Achtung: Vor Installations- oder Servicearbeiten, Stromversorgung unterbrechen, um Unfälle zu vermeiden.




Attention: Avant le montage et la mise en service, couper l'alimentation secteur pour éviter toutes décharges.

Atención: Desconéctese de la corriente eléctrica, antes de la instalación o del servicio, a fin de impedir sacudidas eléctricas.

Attenzione: Per prevenire infortuni, togliere tensione prima dell'installazione o manutenzione.



IEC/EN 60947-4-1/5-1
UL 508
CSA 22.2 No. 14




IEC 60947-4-1/-5-1
EN 60947-4-1/-5-1

CI 5	gG	max.	
		Type 1	Type 2
	05	35 A	16 A
	09	35 A	20 A
	12	35 A	20 A


CI 5



10 mm



Danfoss
37-312.10




2 x 0.75 ... 2.5 mm²
No. 18 ... 12 AWG



Use 75°C Cu wire only




1... 1.2 Nm
8.9... 10.6 lb-in



Danfoss
37-313.10

USA/ CDN


Suitable for use on circuits capable of delivering max. 5000 rms sym. A, 600 V



Danfoss
37-314.10


037C3055

037C3055



*)

- Mindst afstand mellem jordede dele eller vægge.
- Minimum distance to grounded parts or walls.
- Minimaler Abstand gegen geerdete Teile oder Wände.
- Distance minimale envers pièces mises à terre ou parois.
- Distancia minima a chasis o paredes.
- Distanza minimale per pezzi a massa o pareti.



©Danfoss A/S 02-2008 (AC-BNM/mr)