

New Products – Introduction of SC-FTX

We are pleased to introduce our latest development within the Danfoss R134a range of compressors:

SC12FTX	SC15FTX
R134a -115 V/60 Hz	R134a -115 V/60 Hz
LBP	LBP
1280 Btu/h*	1550 Btu/h*
3.55 Btu/Wh*	3.83 Btu/Wh*

* Test conditions	ASHRAE
Condensing temperature	130°F (54.4°C)
Ambient and suction gas temp.	90°F (32°C)
Liquid temperature	90°F (32°C)

If you should need any samples of the new SC-FTX units, do not hesitate to contact your usual Danfoss Compressors contact person.

Direct weblink to the SC12FTX and SC15FTX data sheets:

www.danfoss.com/compressors/products/R134a_115V_60Hz/s-series.htm

Please also visit our web site:

www.danfoss.com/compressors

and have a look at our complete product programme covering all your present and future applications, news and literature.



SC-FTX features:

- Improved LBP performance
- Improved valve design
- Strong motor
- Ideal for general use and in areas with unstable power supply



Danfoss Compressors GmbH

Mads-Clausen-Strasse 7
Postfach 1443, D-24939 Flensburg
Telefon: (0461) 4941-0
International +49 461 4941-0
Telefax: +49 461 44715
Telex: 227 43 dancom d

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed.
All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.