



Danfoss A/S  
Refrigeration Controls  
Albuen 29  
DK-6000 Kolding  
Denmark

**Danfoss A/S**  
DK-6430 Nordborg  
Danmark  
CVR nr.: 20 16 57 15  
Telefon: +45 7488 2222  
Fax: +45 7449 0949

## MANUFACTURER'S DECLARATION Danfoss A/S

Declares under our sole responsibility that the product(s)

**Solenoid valve type EVR**

**Type EVR 2, EVR 3, EVR 4, EVR 6, EVR 8, EVR 10, EVR 15, EVR 18, EVR 20**

Covered by this declaration is in conformity with the following directive(s), standard(s) or other normative document(s), provided that the product is used in accordance with our instructions.

### Pressure Equipment Directive 97/23/EC

- EN 12284 : 2003 Refrigerating systems and heat pumps-Valves -Requirements, testing and marking
- EN12165 : 2011 Copper and copper alloys – Wrought and unwrought forging stock
- EN12449 : 2012 Copper and copper alloys – Seamless round tubes for general purpose.
- EN 10088-1 : 2005 List of stainless steel
- EN 10088-2 : 2005 Technical delivery conditions for sheet/plate and stripe of corrosion resisting steel and bright.
- EN 10088-3 : 2005 Technical delivery conditions for semi-finished products, bars, rod, wire, sections and bright Products of corrosion resisting steels for general purpose.


Fluid group Group II Nontoxic, non-flammable refrigerant

Maximum Working Pressure:

EVR 2 to EVR 8	: 45.2 barg (655 psig)
EVR 10	: 35 barg (507psig)
EVR 15 to EVR 20	: 32 barg (465 psig)

Nominal bore: DN 6 - 28 (¼ - 1 ½ inch):

We hereby declare that mentioned equipment is covered by Article 3, paragraph 3.

Date 2013-01-18	Issued by Sun Jing	Date 2013-01-18	Approved by 
--------------------	-----------------------	--------------------	--

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation