



ELIMINATOR®  
Liquid line filter drier



993B9855

Solid core liquid line filter drier 05 cu in.																		
Refrigeration and Air Conditioning																		
Type	Connection	Liquid capacity [kW] / [TR]						Drying capacity [kg] / [lbs], t = 24 °C										
		R 134A	R 404A	R 507	R 22	R 407C	R 410A	R 134A	R 404A	R 507	R 22	R 407C	R 410A					
DML/DCL 052	1/4 in. flare	7.67 / (2.18)	5.62 / (1.60)	5.45 / (1.55)	8.45 / (2.40)	8.02 / (2.28)	8.32 / (2.37)	DML: 7.9 / (17.4)  DCL: 6.2 / (13.6)	DML: 8.5 / (18.7)  DCL: 6.6 / (14.6)	DML: 8.6 / (19.1)  DCL: 6.7 / (14.9)	DML: 8.0 / (17.6)  DCL: 6.2 / (13.8)	DML: 7.9 / (17.5)  DCL: 6.2 / (13.6)	DML: 7.2 / (15.9)  DCL: 5.6 / (12.4)					
DML/DCL 052S	6 mm or 1/4in. ODF																	
DML/DCL 052.5S	8 mm or 5/16 in. ODF	9.58 / (2.72)	7.01 / (1.99)	6.80 / (1.93)	10.54 (3.00)	11.01 / (2.85)	10.38 / (2.95)											
DML/DCL 053	3/8 in. flare	12.87 / (3.66)	9.81 / (2.79)	9.52 / (2.71)	14.44 / (4.10)	13.80 / (3.92)	14.58 / (4.15)											
DML/DCL 053S	10 mm or 3/8 in. ODF																	
DML/DCL 054	1/2 in. flare	25.70 / (7.31)	20.77 / (5.91)	20.19 / (5.74)	29.64 / (8.43)	28.62 / (8.14)	31.07 / (8.83)											
DML/DCL 054S	12 mm or 1/2 in. ODF																	
DML/DCL 055	5/8 in. flare	36.22 / (10.30)	29.07 / (8.26)	28.25 / (8.03)	41.63 / (11.84)	40.15 / (11.42)	43.45 / (12.35)											
DML/DCL 055S	16 mm or 5/8 in. ODF																	

ELIMINATOR®

The Danfoss ELIMINATOR® Series of filter driers are the most effective all-purpose driers available today. Choose the core composition that's right for your system:

DML - 100% molecular sieve. Designed for applications requiring the highest moisture capacity.

DCL - 80% molecular sieve with 20% activated alumina. Designed for applications requiring high moisture capacity and acid adsorption capacity.