



ELIMINATOR®
Receiver filter drier

Solid core receiver filter drier 20 cu in.												
Refrigeration and Air Conditioning												
Type	Liquid capacity [kW] / [TR]						Drying capacity [kg of refrigerant], t = 24 °C					
	R 134A	R 404A	R 507	R 22	R 407C	R 410A	R 134A	R 404A	R 507	R 22	R 407C	R 410A
DMC/DCC 2032S	7.71	5.52	5.36	8.44	7.96	8.21	DMC: 5.0	DMC: 5.3	DMC: 5.4	DMC: 5.0	DMC: 5.0	DMC: 4.5
DMC/DCC 2033S	15.69	11.17	10.84	17.14	16.14	16.61						
DMC/DCC 2034S	32.65	25.73	25.05	37.42	35.85	36.68	DCC: 3.9	DCC: 4.2	DCC: 4.2	DCC: 3.9	DCC: 3.9	DCC: 3.5



ELIMINATOR®

The Danfoss ELIMINATOR® Series of filter driers are the most effective all-purpose driers available today. Choose the core composition that's right for your system:

DMC – 100% molecular sieves. Designed for applications requiring the highest moisture capacity.

DCC – 80% molecular sieves with 20% activated alumina. Designed for applications requiring high moisture capacity and acid adsorption capacity.



993B9969