



993B9970

Solid core receiver filter drier 40 cu in.												
Refrigeration and Air Conditioning												
Type	Liquid capacity [kW] / [TR]						Drying capacity [kg of refrigerant], t = 24 °C					
	R 134A	R 404A	R 507	R 22	R 407C	R 410A	R 134A	R 404A	R 507	R 22	R 407C	R 410A
DMC/DCC 40163S	15.69	11.17	10.84	17.14	16.14	16.61	DMC: 27.7	DMC: 29.8	DMC: 30.4	DMC: 28.1	DMC: 27.8	DMC: 25.3
DMC/DCC 40164S	32.65	25.73	25.05	37.42	35.85	38.68	DCC: 21.6	DCC: 23.3	DCC: 23.7	DCC: 21.9	DCC: 21.7	DCC: 19.7

ELIMINATOR®

The Danfoss ELIMINATOR® Series of filter driers are the most effective all-purpose driers available today. Choose the core composition that's right for your system:

DMC – 100% molecular sieves.
Designed for applications requiring the highest moisture capacity.

DCC – 80% molecular sieves with 20% activated alumina. Designed for applications requiring high moisture capacity and acid adsorption capacity.