



a	12.01.10	KOR/BRE	part-no. added			
	date	name	amendment			

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4
checked	18.11.09	Bremer	Bremer	format	A4
	date	name	signature	DIN ISO 5456	
				all dimensions mm	

Dimensions B 0908112
du/dt filter 105A – IP00

order number	drawing number	modi.	sheet
130B2841	Z790911014	a	1/1

Please observe protection clause to DIN 34