

1 2 3 4 5 6 7 8

A

B

C

D

E

F

A





B

C

D

E

F



a	12.01.10	KOR/BRE	part-no. added			
	date	name	amendment			

Dimensions toleranced according to ISO 2768-m						
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	± 0.1	± 0.1	± 0.2	± 0.3	± 0.5	± 0.8

drawn	18.11.09	Kornau	Kornau	scale	1:4
checked	18.11.09	Bremer	Bremer	format	A4
	date	name	signature		
				DIN ISO 5456	
				all dimensions mm	

Dimensions B 0908113
du/dt filter 160A – IP00

order number	drawing number	modi.	sheet
130B2844	Z790911016	a	1/1

Please observe protection clause to DIN 34

1 2 3 4 5 6 7 8