



additional informations:
 filter colour : RAL 7001
 filter weight : 61,8kg
 accessories : 2x 130B4045
 label:

VLT MCC 102 du/dt FILTER
 www.danfoss.com

ENTERAS A/S, Aalborgvej 10, 8260 Ålbæk, Denmark
 L-5014H
 Fax: +45 78 28 24 60
 E-mail: vlt@danfoss.com
 Danfoss A/S, 11800 Omaha, NE, USA
 Fax: +1 408 485 1131
 E-mail: vlt@danfoss.com

130B2846001057 206

Use only with a type 1 or type 2 series two-pole contact device
 Terminal e to 120mm
 City/CL

E 2 3922
 81 020605
 118 118 118 118

CE

cl 17.05.16 Schr./File. type/able updated. Danfoss Postaddress included
 B 26.11.14 Schr./File. type/able updated
 A 30.09.10 KOR/Lauer name approval added
 date amendment

Dimensions toleranced according to ISO 2768-m					
Tolerance class	0.5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400
	±0.1	±0.1	±0.2	±0.3	±0.5
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5

drawn	12.05.10	Kornau	Kornau	scale	1:6
checked	12.05.10	Bremer	Bremer	format	A4
date		name	signature	DIN ISO	5456

all dimensions mm

Dimensions B 1003009
 du/dt filter 160A – IP54

order number	130B2846	drawing number	Z791004024	modi.	C	sheet	1/1
Please observe protection clause to ISO 16016							