









- contents:
- 1 pcs filter cover (RAL 7001)
  - 1 pcs terminal cover (RAL 7001)
  - 1 pcs screen connection plate (zink plated steel)
  - 2 pcs cable clamp 130B4045
  - 4 pcs screws M4x25
  - 2 pcs earth screws M6x16 (with lockwasher and washer)

04.10.13 | Wenz./BRE | dimension 130mm (old 115mm)  
 date | name | amendment



Dimensions toleranced according to ISO 2768-m					
Tolerance class	0,5 to 3	3 to 6	6 to 30	30 to 120	120 to 400
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5

drawn	12.05.10	Kornau	Kornau	scale	1:4
checked	12.05.10	Bremer	Bremer	format	A3
	date	name	signature		

NEMA kit  
 80/105A du/dt filter

order number 130B4181  
 drawing number Z791005007

Please observe protection clause to DIN 34

modi: a  
 sheet 1/1

1 2 3 4 5 6 7 8