




- contents:
- 1 pcs filter cover (RAL 7001)
 - 1 pcs terminal cover (RAL 7001)
 - 1 pcs screen connection plate (zink plated steel)
 - 2 pcs cable clamp 130B4045
 - 4 pcs screws M4x25
 - 2 pcs earth screws M6x16
- (with lockwasher and washer)




a|04.10.13 | Wenz-/BRE | dimension 180mm (old 125mm)

date | name | amendment





terminal cover



filter cover



screen connection plate



Dimensions toleranced according to ISO 2768-m						
Tolerance class	0,5 to 3	from 3 to 6	from 6 to 30	from 30 to 120	from 120 to 400	from 400 to 1000
m (middle)	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8

drawn	12.05.10	Kornau	Kornau	scale	1:6
checked	12.05.10	Bremer	Bremer	format	A3
date		name	signature	DIN ISO 5456	

NEMA kit
160A du/dt filter

order number 130B4182
drawing number Z791005008

Please observe protection clause to DIN 34