

| HORSEPOWER VALUES |               |              |              | DIMENSIONS inches [mm] |                 |                  |                 |                |                   |              |               |                |                 |               |               | FIG. |
|-------------------|---------------|--------------|--------------|------------------------|-----------------|------------------|-----------------|----------------|-------------------|--------------|---------------|----------------|-----------------|---------------|---------------|------|
| 208V              | 230V          | 460V         | 600V         | H                      | W               | D                | a               | b              | c                 | d            | e             | f              | g               | h             | i             |      |
| 0.5HP - 3.0HP     | 0.5HP - 3.0HP | 0.5HP - 10HP | 0.5HP - 10HP | 30.0<br>[761.8]        | 28.8<br>[732.1] | 11.0<br>[278.6]  | 20.0<br>[508.3] | 4.6<br>[116.9] | 31.25<br>[793.8]  | 1.77<br>[45] | 3.1<br>[78.5] | 6.9<br>[175.3] | 12.0<br>[304.8] | 2.0<br>[50.8] | 2.0<br>[50.8] | 1    |
| 5.0HP - 10HP      | 5.0HP - 10HP  | 15HP - 25HP  | 15HP - 25HP  | 38.0<br>[967]          | 31.1<br>[790]   | 12.25<br>[310.3] | 22.0<br>[559]   | 4.5<br>[113.5] | 39.25<br>[996.8]  | 1.77<br>[45] | 3.1<br>[78.5] | 8.2<br>[208]   | 9.7<br>[246]    | 2.0<br>[50.8] | 2.0<br>[50.8] | 1    |
| 15HP - 20HP       | 15HP - 20HP   | 30HP - 40HP  | 30HP - 40HP  | 38.0<br>[967]          | 31.1<br>[790]   | 12.25<br>[310.3] | 22.0<br>[559]   | 4.5<br>[113.5] | 39.25<br>[996.8]  | 1.77<br>[45] | 3.1<br>[78.5] | 8.2<br>[208]   | 9.7<br>[246]    | 2.0<br>[50.8] | 2.0<br>[50.8] | 2    |
| 25HP - 30HP       | 25HP - 30HP   | 50HP - 75HP  | 50HP - 75HP  | 47.0<br>[1196]         | 38.2<br>[970.4] | 16.00<br>[406.4] | 29.0<br>[736.6] | 4.6<br>[116.9] | 48.25<br>[1225.4] | 1.77<br>[45] | 3.1<br>[78.5] | 10.2<br>[259]  | 14.25<br>[362]  | 2.0<br>[50.8] | 2.0<br>[50.8] | 2    |

FIGURE 1










FIGURE 2




DIMENSIONS ARE NOT FOR MANUFACTURING PURPOSES

|     |            |      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |     |                                    |     |             |        |
|-----|------------|------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|------------------------------------|-----|-------------|--------|
| B   |            |      | <p align="center">- NOTICE -</p> <p>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES, SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.</p> | DRN | NAME                               |     |             |        |
| A   | SP10079    | 7/10 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | DTM | INSTALLATION / DIMENSIONAL DRAWING |     |             |        |
| DR  | ECNSP07050 | 8/07 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | APR | NEMA 3R                            |     |             |        |
| REV | ECN        | DATE |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | DTM | MODEL                              | VLT | PAGE 1 OF 2 | SIZE A |

DIMENSIONS ARE IN INCHES [MILLIMETERS]



DIMENSIONS ARE NOT FOR MANUFACTURING PURPOSES

|     |            |      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |     |                                    |     |             |                                                                                       |
|-----|------------|------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|------------------------------------|-----|-------------|---------------------------------------------------------------------------------------|
| B   |            |      | THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES, SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST. | DRN | NAME                               |     |             |  |
| A   | SP10079    | 7/10 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | DTM | INSTALLATION / DIMENSIONAL DRAWING |     |             |                                                                                       |
| DR  | ECNSP07050 | 8/07 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | APR | NEMA 3R                            |     |             |                                                                                       |
| REV | ECN        | DATE |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | DTM | MODEL                              | VLT | PAGE 2 OF 2 | SIZE A                                                                                |