



NOTES:

- *INDICATES COMPONENTS NOT SUPPLIED BY FACTORY.
- FEEDER CIRCUIT PROTECTION AND INPUT AND MOTOR WIRING MUST BE SELECTED IN ACCORDANCE WITH THE N.E.C. ANY APPLICABLE LOCAL CODES AND THE DRIVE PANEL NAMEPLATE RATING. DANFOSS RECOMMENDS AN INSULATED BONDING WIRE FROM MOTOR TO DRIVE RUNNING WITH MOTOR LEADS INSIDE CONDUIT OR SHIELDED CABLE.
- REPLACE JUMPER WITH N.C. SAFETY INTERLOCK CONTACT AS APPLICABLE.
- REFER TO THE INSTALLATION OPERATION MANUAL FOR THE PROPER DRIVE FUSING. DRIVE FUSES ARE INTERNAL TO DRIVE ON UNITS > 125 HP.
- ADD JUMPER TO ENABLE AUTO BYPASS FUNCTION.
- JUMPER FROM H2 TO H3 IS NOT PRESENT ON TRANSFORMER PRIMARY FOR 575V INPUT..
- REMOVE JUMPER TO ENABLE DAMPER FEEDBACK IN FIRE MODE.
- ADD JUMPER TO FORCE BYPASS IN FIRE MODE.
- MOTOR/LINE AND CONDUIT GROUND CONNECTIONS TO BE MADE ON CABINET GROUND BAR.

NOTE: ALL DRIVE WIRES #18 AWG BLUE UNLESS OTHERWISE NOTED
NOTE: ANALOG PAIRS ARE 18 AWG BELDEN #9460

		3						- NOTICE -		DRN		TOLERANCE		NAME		POWER DISTRIBUTION WIRING DIAGRAM PHD PANEL HVAC 3-CONTACTOR BYPASS 460/575 VAC FUDED DISC., TYPE 1/12, WITH DV/DT FILTER		 DWG. NO. 174N9958			
		2						THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES, SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.		SJG		Unless Otherwise Specified		MODEL						FC102	
RELEASE		0		SP14067		11/05/14				APR		2 PLC: ±.02 3 PLC: ±.005									
DESCRIPTION		REV		ECN		DATE				SJG		SCALE 1.0									



NOTE: ALL WIRES ARE #16 AWG RED UNLESS OTHERWISE NOTED

- NOTICE -

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES, SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.

DESCRIPTION	REV	ECN	DATE
RELEASE	0	SP14067	11/05/14

DRN	SJG	TOLERANCE	NAME		CONTROL WIRING DIAGRAM	
APR	SJG	Unless Otherwise Specified	PHD PANEL HVAC 3-CONTACTOR BYPASS 460/575 VAC		FUSED DISC., TYPE 1/12, WITH DV/DT FILTER	
		2 PLC ±.02 3 PLC ±.005	MODEL	FC102	SHEET 2 OF 2	SIZE D
		SCALE 1.0			DWG. NO.	174N9958

