



FRAME SIZE A5			
VOLTAGE	HP	KW	
208/230	0.5-5	0.75-3.7	
460/600	0.5-10	0.75-7.5	

- 1) 3X PLACE CONDUITS IN PRE-EXISTING CONDUIT HOLES. IF NOT USED, PLUG HOLES WITH NEMA TYPE 12 HOLE PLUGS.
- 2) FOR NEMA TYPE 12 UNITS USE NEMA TYPE 12 CONDUITS AND HUBS

NOTICE:

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES. SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANY OTHER PERSON WITHOUT THE WRITTEN PERMISSION OF DANFOSS DRIVES, AND SHALL BE RETURNED UPON REQUEST.

LATEST E.C.N. NO.:		E.C.N. PRO-E ENTRY BY/DATE:		PLOT SCALE:		PRO-E ENTRY BY/DATE:		CHECKED BY/DATE:		TITLE:	
				NONE		12/20/06		12/20/06		DWG, REF, SUBMITTAL, A5-TIER 1	
						176U5289		176U5289		DANFOSS DRIVES 4401 N. BELL SCHOOL RD. LITTLE ROCK, AR 72116-5111 USA (815) 539-8500 FAX (815) 539-8000	
										REV.:	