


LEGEND:
 132kW = FC-302 P132 T5
 FC-202 P160 T4
 FC-102 P160 T4
 160kW = FC-302 P160 T5
 FC-202 P200 T4
 FC-102 P200 T4
 200kW = FC-302 P200 T5
 FC-202 P250 T4
 FC-102 P250 T4



NOTICE

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. UNLESS OTHERWISE SPECIFIED, ALL RIGHTS ARE RESERVED. THE INFORMATION CONTAINED HEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. NO PART OF THIS DOCUMENT IS TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF DANFOSS DRIVES. ANY UNAUTHORIZED REPRODUCTION OR TRANSMISSION OF THIS DOCUMENT IS STRICTLY PROHIBITED.

DESIGN ECN NO.: ECN HP08005 ECKM CAD ENTRY BY/DATE: T.H. 04/16/08

CAD ENTRY BY/DATE: I. HANSON 03/10/07
 DESIGNED BY/DATE: WFS APPROVAL BY/DATE: I. HANSON 05/10/07
 PLOT SCALE: 1:1

CHECKED BY/DATE: A77R0041.DWG
 DATE APPROVAL BY/DATE: DWG. APPROVAL BY/DATE: TITLE: DWG. BLOCK DIAGRAM, FC. D2/D4 FRAME, T4/T5
 SHEET: 1 OF 1 DRAWING NO.: 177R0041 REV.: A

DANFOSS DRIVES
 4501 N. BELL BLVD., SUITE 400
 WILSON, CA 95690 FAX (916) 438-8000

4 3 2 1