



LEGEND:

160kW = FC-302 P160 T7	250kW = FC-302 P250 T7
FC-202 P200 T7	FC-202 P315 T7
FC-102 P200 T7	FC-102 P315 T7
200kW = FC-302 P200 T7	315kW = FC-302 P315 T7
FC-202 P250 T7	FC-202 P400 T7
FC-102 P250 T7	FC-102 P400 T7



4
3
2
1

A
B
C
D



4
3
2
1

A
B
C
D

NOTICE

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. THE INFORMATION CONTAINED HEREIN IS THE PROPERTY OF DANFOSS DRIVES. THE INFORMATION CONTAINED HEREIN IS NOT TO BE DISCLOSED TO ANY OTHER PARTY WITHOUT THE WRITTEN PERMISSION OF DANFOSS DRIVES. ANY DISCLOSURE OF THIS INFORMATION TO ANY OTHER PARTY WITHOUT THE WRITTEN PERMISSION OF DANFOSS DRIVES IS STRICTLY PROHIBITED.

DESIGN BY/DATE	DESIGNED BY/DATE	CHECKED BY/DATE
1. HANSON 05/10/07	1. HANSON 05/10/07	
APP. BY/DATE	APP. BY/DATE	
DRG. FILE	DRG. APPROVAL BY/DATE	
A77R0045.DWG		
SHEET	1	DRAWING NO.
1	1	177R0045
REV.	A	

DANFOSS DRIVES
4601 N. BELT ROAD
(913) 634-8000 Fax (913) 634-8000

LOAD SHARE OPTION

TB4
TB4-DIC