

**Danfoss A/S**6430 Nordborg
Denmark
CVR nr.: 20 16 57 15Telephone: +45 7488 2222
Fax: +45 7449 0949**EU DECLARATION OF CONFORMITY****Danfoss A/S****Danfoss Drives**

declares under our sole responsibility that the

Product category: Soft Starters

Type designation(s): MCD 20w-xxx-Ty-CVz.

Where 20w designates the features of the starter

201 = soft start only or, 202 = soft start plus motor protection

xxx = designates the Nominal Motor Rating, 007 kW to 110 kW,

T4 = 440 VAC or, T6 = 575 VAC

CVz = designates Control Supply Voltage

CV1 = 24 VAC. CV3 = 110 to 240 VAC and 380 to 440 VAC

Covered by this declaration is in conformity with the following directive(s), standard(s) or other normative document(s), provided that the product is used in accordance with our instructions.

Low Voltage Directive 2014/35/EU

EN60947-4-2 (2012)

Low-voltage switchgear and controlgear. Contactors and motor-starters. AC semiconductor motor controllers and starters.

EMC Directive 2014/30/EU

EN60947-4-2 (2012)

Low-voltage switchgear and controlgear. Contactors and motor-starters. AC semiconductor motor controllers and starters.

RoHS Directive 2011/65/EU including amendment 2015/863.

EN IEC63000:2018

Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.

Date: 2021.11.12 Place of issue:	Issued by	Date: 2021.11.12 Place of issue:	Approved by
Graasten, DK	 Signature: Martin Skov Holm Name: Martin Skov Holm Title: Head of PM - EU	Graasten, DK	 Signature: Michael Quitzau Name: Michael Quitzau Title: Head of PM&D, Denmark

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation



Danfoss A/S

6430 Nordborg
Denmark
CVR nr.: 20 16 57 15

Telephone: +45 7488 2222
Fax: +45 7449 0949

UK DECLARATION OF CONFORMITY

Danfoss A/S

Danfoss Drives

declares under our sole responsibility that the

Product category: Soft Starters

Type designation(s): MCD 20w-xxx-Ty-CVz.

Where 20w designates the features of the starter

201 = soft start only or, 202 = soft start plus motor protection

xxx = designates the Nominal Motor Rating, 007 kW to 110 kW,

T4 = 440 VAC or, T6 = 575 VAC

CVz = designates Control Supply Voltage

CV1 = 24 VAC. CV3 = 110 to 240 VAC and 380 to 440 VAC

Covered by this declaration is in conformity with the following regulation(s), standard(s) or other normative document(s), provided that the product is used in accordance with our instructions.

Electrical Equipment (Safety) Regulations 2016

BS EN60947-4-2 (2012)

Low-voltage switchgear and controlgear. Contactors and motor-starters. AC semiconductor motor controllers and starters.

Electromagnetic Compatibility Regulations 2016



BS EN60947-4-2 (2012)

Low-voltage switchgear and controlgear. Contactors and motor-starters. AC semiconductor motor controllers and starters.

The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 as amended

BS EN IEC63000:2018

Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.

Date: 2021.11.12 Place of issue: Graasten, DK	Issued by Signature:  Name: Martin Skov Holm Title: Head of PM - EU	Date: 2021.11.12 Place of issue: Graasten, DK	Approved by Signature:  Name: Michael Quitzau Title: Head of PM&D, Denmark
---	--	---	---

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation