



**Danfoss A/S**

6430 Nordborg

Denmark

CVR nr.: 20 16 57 15

Telephone: +45 7488 2222

Fax: +45 7449 0949

**EU DECLARATION OF CONFORMITY**

**Danfoss A/S**

**Danfoss Drives**

declares under our sole responsibility that the

**Product category:** Frequency Converter

**Type designation(s):** FC-350HXXXT4\*\*\*\*\*

Character XXX: K37, K55, K75, 1K1, 1K5, 2K2, 3K0, 4K0, 5K5, 7K5, 11K, 15K, 18K, 22K, 30K, 37K, 45K, 55K, 75K

The meaning of the 39 characters in the type code string can be found in appendix 00765728.

Covered by this declaration is in conformity with the following directive(s), standard(s) or other normative document(s), provided that the product is used in accordance with our instructions.

**Low Voltage Directive 2014/35/EU**

EN61800-5-1:2007 + A1:2017

Adjustable speed electrical power drive systems – Part 5-1: Safety requirements – Electrical, thermal and energy.

**EMC Directive 2014/30/EU**


EN61800-3:2004 + A1:2012

Adjustable speed electrical power drive systems – Part 3: EMC requirements and specific test methods.

**RoHS Directive 2011/65/EU including amendment 2015/863**

EN IEC 63000: 2018

Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.

<p>Date: 2021.11.22 Place of issue: Beijing, CN</p>	<p>Issued by  <b>Signature:</b> <b>Name: Lv Jian</b> <b>Title: Director, Product Management China</b></p>	<p>Date: 2021.10.22 Place of issue: Beijing, CN</p>	<p>Approved by  <b>Signature:</b> <b>Name: Holst Bo Kjargaard</b> <b>Title: Head of PM&amp;D China</b></p>
---	--	---	---

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation