









Basic Unit

Connections	Max Cabel size	AWG Size
Mains	50 mm ²	22
Motor	40 mm ²	24
Control	30 mm ²	26

Type	Value
Max Weight	10.5 kg / 22 lb
IP Class	IP20
Nema Class	Type 20



THIS DRAWING SHOW THE MOST COMMEN VERSION OF THIS VARIANT.
SMALL DIFFERENCES CAN OCCUR DEPENDING ON YOU FINALE CONFIGURATIONS.

CENTER OF GRAVITY:
REFERENCE ONLY, CONFIGURATIONS MAY SHIFT CG IN ALL THEE AXISSES

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1mm (0.4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		FIRST ANGLE PROJECTION	SCALE	SIZE	MATERIAL
			1:5	A3	
		FINISH			
		DESCRIPTION			
CHANGED					
DESIGNED	- 2013-05-17				
CHECKED					
CONFIDENTIAL: PROPERTY OF DANFOSS A/S NORDBOG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.		DRAWING NUMBER		REV	
		A3			
		MODEL		SHEET	
		FC_300_A3_ENCLOSURE_IP20_3D_STE		1 OF 1	