


RJ45
8x8


| SIGNAL | M12 PIN # | RJ45 |
|--------|-----------|------|
| RX+ | 1 | 1 |
| TX+ | 2 | 3 |
| RX- | 3 | 2 |
| TX- | 4 | 4 |

EtherNet/IP Connectors



Ethernet Port 1

Ethernet Port 2



| | | | |
|-----|----------|---------|--|
| B | | | |
| A | | | |
| DR | 2016XXXX | 7/14/16 | |
| REV | ECN | DATE | |

| | |
|---------|-----|
| DRN | PCN |
| 7/13/16 | MJM |
| APR | |
| 7/13/16 | |

| | |
|-------------------------|-------------------|
| NAME | MODEL: |
| SCHEMATIC DIAGRAM | FC102/202/301/302 |
| MCA 120 Profinet Option | |

| | |
|------|----|
| PAGE | OF |
| 1 | 1 |

| | |
|------|---------|
| SIZE | DWG NO. |
| A | |



— NOTICE —
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES. SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.