









Type	Value
Max Weight	4.9 kg / 10.8 lb
IP Class	IP20 A
Nema Class	CHASSIS



MOUNTING BASE



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

● CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±0.1MM (0.004 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH).		FIRST ANGLE PROJECTION	SCALE 1:2	DRAWING MATERIAL SIZE A2	FINISH	
CHANGED				DESCRIPTION MCAD A2 IP20 A		
DESIGNED	DANFOSS					27-11-2015
CHECKED						
PROPERTY OF DANFOSS A/S HØRNBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				DRAWING NUMBER MCAD-A2-IP20-A	REV 001	
				MODEL MCAD-A2-IP20-A	1 OF 1	