









Type	Value
Max Weight	7.0 kg / 15.4 lb
IP Class	IP21 B
Nema Class	Type 1



DETAIL A
SCALE 1:1



DETAIL B
SCALE 1:1



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1MM (0.4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH)				FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
					1:2	A1	
				FINISH			
				DESCRIPTION			
CHANGED							
DESIGNED	DANFOSS	09-01-2016					
CHECKED							
				DRAWING NUMBER		REV	
				MCAD-A3-IP21-B		001	
				MODEL		SHEET	
				MCAD-A3-IP21-B		1 OF 1	
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.							