









Type	Value
Max Weight	51 kg / 112.44 lb
IP Class	IP20
Nema Class	Chassis



DETAIL A  
SCALE 1:1



DETAIL B  
SCALE 1:1



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.  
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:  
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS $\pm 1\text{MM}$ [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE	DRAWING SIZE	MATERIAL
			1:5	A2	
		FINISH			
		DESCRIPTION			
		MCAD H8 IP20			
CHANGED					
DESIGNED	DANFOSS	27-11-2015			
CHECKED					
PROPERTY OF DANFOSS A/S NORDBOURG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.		DRAWING NUMBER		REV	
		MCAD-H8-IP20		001	
		MODEL		SHEET	
		MCAD-H8-IP20		1 OF 1	

