









Type	Value
Max Weight	45 kg / 99.21 lb
IP Class	IP54
Nema Class	Type 12



DETAIL A
SCALE 1:1



DETAIL B
SCALE 1:1



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT.
SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY:
FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ±1MM [0.4 INCH]. ALL DIMENSIONS ARE IN MILLIMETERS [INCH]		FIRST ANGLE PROJECTION	SCALE 1:5	DRAWING SIZE A2	MATERIAL	
					FINISH	
					DESCRIPTION	
CHANGED					MCAD I7 IP54	
DESIGNED	DANFOSS 27-11-2015					
CHECKED					DRAWING NUMBER	
					MCAD-17-IP54	
					REV 001	
					MODEL	
					MCAD-17-IP54	
					SHEET 1 OF 1	