


B		
A		
DR	2016XXXX	7/14/16
REV	ECN	DATE

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF DANFOSS DRIVES. IT IS LOANED BY DANFOSS DRIVES SUBJECT TO THE CONDITIONS THAT IT AND THE INFORMATION EMBODIED THEREIN SHALL BE USED ONLY FOR RECORD AND REFERENCE PURPOSES. SHALL NOT BE USED OR CAUSED TO BE USED IN ANY WAY PREJUDICIAL TO THE INTERESTS OF DANFOSS DRIVES. SHALL NOT BE REPRODUCED OR COPIED IN WHOLE OR IN PART, OR DISCLOSED TO ANYONE WITHOUT THE DIRECT WRITTEN PERMISSION OF DANFOSS DRIVES AND SHALL BE RETURNED UPON REQUEST.

DRN	PCGN
APR 7/13/16	MJM
7/13/16	

MODEL	NAME
FC-102,202,301,302	SCHEMATIC DIAGRAM
PAGE 1 OF 1	MCB 114 Sensor Input Option
SIZE A	
DWG NO.	




MCB 114
Sensor Input

Option B

SW. ver.xx.xx

Code No. 130B1272



<u>Terminal</u>	<u>Name</u>	<u>Function</u>
1	VDD	24VDC to supply 4-20mA sensor
2	I in	4-20mA input
3	GND	Analog input GND
4,7,10	Temp 1,2,3	Temperature input
5,8,11	Wire 1,2,3	3rd wire input if 3 wire sensors are used
6,9,12	GND	Temp. input GND