



Danfoss A/S

DK-6430 Nordborg
Denmark
CVR nr.: 20 16 57 15

Telephone: +45 7488 2222
Fax: +45 7449 0949

MANUFACTURER'S DECLARATION

Danfoss A/S

Danfoss Drives

declares under our sole responsibility that the **VLT® HVAC Drive Series FC-102**

Typecodes:

FC-102XYYYT4EZZ*****

Where:

X: N or P.



YYY: 11K, 15K, 18K, 22K, 30K, 37K, 45K, 55K, 75K, 90K, 110, 132, 160, 200, 250 or 315.

ZZ: E21, E55, E66, E3R, P3R, P21, P55, P66, C20, E20, E21, E54, E2M, E5M, H21 or H54.

That representative drives have successfully been tested to be able run for more than 1 h:
at the following conditions:

- 70°C ambient temperature.
- Full load on versions up to and 90KW(P), and from 110KW versions (N) is the load derated to 80% of drive's nominal current.
- Firemode enabled.

The meaning of the 39 characters in the type code string can be found in appendix 00729776.

Date: 14/8 2018	Issued by Signature  Name: Leo Birkkjar Lauritsen Title: Head of P400 Group	Date: 16/8-2018	Approved by Signature  Name: Michael Termansen Title: VP, Design Center DK and DE
-----------------------	---	--------------------	---

Danfoss only vouches for the correctness of the English version of this declaration. In the event of the declaration being translated into any other language, the translator concerned shall be liable for the correctness of the translation.