



* Set point Sollwert

Drive signal start active [123]
FU Signal Start aktiv [123]

* Current input, 0-20mA and 4-20mA
Stromeingang, 0-20 mA und 4-20 mA
Voltage input, -10 - +10 V DC
Spannungseingang -10 - +10 V DC

4				Commission		Danfoss GmbH		Project description		Page description		Project Number		= FC302		Page	
				132KW VFD Panel		VLT Drives EMA, Carl-Legien Strasse 8		Disconnect switch+dudt Filter		Frequency converter		MC_- - - - -		+ N132KW 230V		5	
Date				9/30/2013		36073 Offenbach, Germany		Trennschalter+dudt Filter		Frequenzumrichter		SAP NO		Manufacturer no		Page	
Ed.				RAMKUMAR												31	
Appr				FALCO													
Constr.				KARTHIK													