



-K2
/5.7:E
Static Start/stop command
Statisch Start/Stoppbefehl

Parameter list

Parameter	Description Beschreibung	Value Wert
5-40	Ready	2
5-12	Without function	0

* Current input, 0-20mA and 4-20mA
Stromeingang, 0-20 mA und 4-20 mA
Voltage input, -10 - +10 V DC
Spannungseingang -10 - +10 V DC

Modification	Date	Name	Contr.

Commission
315KW VFD Panel
 Project description
 Disconnect switch+dudt Filter
 Trennschalter+dudt Filter

Danfoss GmbH
 VLT Drives EMA, Carl-Legien Strasse 8
 63073 Offenbach, Germany



FILE-NAME:
 LOG08300.jpg
 Size 300px x 116px

Page description
Frequency converter
 Frequenzumrichter

Project Number

 SAP NO

= FC302
 + P315KW 230V
 Manufacturer no