



-U1
/2.5:B

VLT FC302 I/O CARD

DISPLAY

-K2
/4.7:E
Start/stop command
Start/Stopbefehl

7.5:E
U1-32

7.5:E
U1-37

* Set point
Sollwert

4.7:C
U1-01

U1-02
4.7:D

Drive signal start active [123]
FU Signal Start aktiv [123]

* Current input, 0-20mA and 4-20mA
Stromeingang, 0-20 mA und 4-20 mA
Voltage input, -10 - +10 V DC
Spannungseingang -10 - +10 V DC

Modification	Date	Name	Contr.	KARTHIK	Commission 110KW VFD Panel Project description Contactor+Fuse+dudt Filter Schütz+Fuse+dudt Filter	Danfoss GmbH VLT Drives EMA,Carl-Legien Strasse 8 63073 Offenbach, Germany		FILE-NAME: LOG008300.jpg Size 300px x 116px	Page description Frequency converter Frequenzumrichter	Project Number MC_ - - - - SAP NO	= FC302 + N110KW 230V Manufacturer no	Page 5 Page 31
--------------	------	------	--------	---------	---	--	--	---	--	---	---	-------------------------