



ic2-30

File Number: E358502**COMPANY****Danfoss Drives A/S**

Ulsnaes 1

Graasten, 6300 Denmark

MODEL INFO

ic2-30 followed by FA, followed by 3N or 1N, followed by 01, 02 or 04, followed by -, followed by 00 through 99, followed by A, followed by 0 through 9, followed by E20 or E21, followed by F0, F2 or F4, followed by +, followed by ACXX or ACBC.

Power Conversion Equipment

POWER CONVERSION EQUIPMENT**VALUE**

UL Standard

UL 61800-5-1

CUL Standard

CAN/CSA C22.2 No. 274

Report Date: 2022-05-31

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2022 UL LLC."