

## **Flow Control Valves Catalog**

Needle Valve, Bi-Directional CP610-1

#### **OPERATION**


This valve is a non-pressure compensated, adjustable flow control valve.

#### Schematic



#### **SPECIFICATIONS**


DIMENSIONS



# Specifications

Rated pressure	210 bar [3000 psi]		
Rated flow at 7 bar	50 l/min		
[100 psi]	[13 US gal/min]		
Leakage	6 drops/min @		
	Rated pressure		
Weight	0.10 kg [0.22 lb]		
Cavity	SDC10-2		

#### Cross-sectional view



### ORDERING INFORMATION

	CP610	) - 1 - <u>В</u> - <u>8</u> S - <u>В</u>	
Seals			
	Seal kit		
B = Buna-N	120073		
V = Viton	120074		
Housing and ports	Housing P/N —		Knob option
0 = No Housing	No Housing		B = Black
DG3B = AL,3/8 BSP	SDC10-2-DG-3B		R = Red
DG4B = AL, 1/2 BSP	SDC10-2-DG-4B		
6S = AL, #6 SAE	CP10-2-6S		
8S = AL, #8 SAE	CP10-2-8S		
Other housings available			