

Flow Control Valves Catalog

Needle Valve, Bi-Directional CP612-2


OPERATION

This valve is a non-pressure compensated, adjustable flow control valve.

Schematic



SPECIFICATIONS




Specifications

Rated pressure	210 bar [3000 psi]
Rated flow at 7 bar	190 l/min
[100 psi]	[50 US gal/min]
Leakage	6 drops/min @
	Rated pressure
Weight	0.48 kg [1.06 lb]
Cavity	SDC16-2

Cross-sectional view DIMENSIONS

mm in



ORDERING INFORMATION

