

Flow Control Valves Catalog

Needle Valve, Bi-Directional CP613-1

OPERATION


This valve is a non-pressure compensated, adjustable flow control valve.

Schematic



SPECIFICATIONS






Specifications	
Rated pressure	210 bar 3000 psi
Rated flow at 7 bar	380 l/min
[100 psi]	[100 US gal/min]
Leakage	6 drops/min @
	Rated pressure
Weight	0.85 kg [1.87 lb]
Cavity	SDC20-2

Cross-sectional view

DIMENSIONS mm in



ORDERING INFORMATION

