FC - 11




Flow Control Valves Catalog

Needle Valve, Bi-Directional CP618-2

OPERATION


This valve is a non-pressure compensated, adjustable flow control valve.

Schematic



SPECIFICATIONS

Theoretical performance




Specifications

Rated pressure	210 bar [3000 psi]
Rated flow at 7 bar	45 l/min
[100 psi]	[12 US gal/min]
Leakage	6 drops/min @
	Rated pressure
Weight	0.09 kg [0.20 lb]
Cavity	SDC08-2

Cross-sectional view

DIMENSIONS

mm in



ORDERING INFORMATION

