


Flow Control Valves Catalog

Adjustable, Restrictive Type CP308-2

OPERATION


This valve is a limited adjustment pressure compensated flow control valve.

Schematic



SPECIFICATIONS

Theoretical performance




Specifications

Rated pressure	210 bar [3000 psi]
Max regulated flow	15 l/min
	[4 US gal/min]
Weight	0.15 kg [0.32 lb]
Cavity	SDC08-2

DIMENSIONS

mm in

Cross-sectional view



ORDERING INFORMATION

