


Flow Control Valves Catalog

Adjustable, Restrictive Type VR 12

OPERATION


This valve is a limited adjustment, pressure compensated, restrictive-type flow control valve.

Schematic



SPECIFICATIONS

Theoretical performance




Specifications

Rated pressure	315 bar [4500 psi]
Max regulated flow	60 l/min
	[16 US gal/min]
Weight	0.44 kg [0.97 lb]
Cavity	NCS12/2

DIMENSIONS

mm in

Cross-sectional view



ORDERING INFORMATION

