


Flow Control Valves Catalog

Fixed Setting, Restrictive Type CP300-1

OPERATION


This valve is a fixed pressure compensated flow control valve.

Schematic



SPECIFICATIONS

Theoretical performance




Specifications

Rated pressure	210 bar [3000 psi]
Max regulated flow	23 l/min
	[6 US gal/min]
Weight	0.12 kg [0.26 lb]
Accuracy ± 20%	0.4-2.2 l/min
	[0.1-0.6 US gal/min]
± 15%	2.3-6.8 l/min
	[0.6-1.8 US gal/min]
± 10%	6.9-22.7 l/min
	[1.8-6 US gal/min]
Cavity	SDC10-2

DIMENSIONS

mm in

Cross-sectional view



ORDERING INFORMATION

1

