

Flow Control Valves Catalog

Velocity Fuse BC 06

OPERATION

SPECIFICATIONS

This is an in-line flow limiter that closes and then provides non-compensated restricted flow when the specified flow setting is exceeded. The valve provides free reverse flow when operated in the opposite direction. Schematic

Theoretical performance

H=0.25

7.5

5

psi

Bar

10 140 105 7.5 5 70-35-2.5

0

0


Pressure drop from P ⇒C according to Adjustment H 26 cSt [121 SUS] hyd.oil at 50°C [122 °F]

H=0.5

H=1


30 I/min

⊓ 8 US gal/min



Specifications

Pressure rating	210 bar 3000 psi
Rated Free Flow	30 l/min 8 US gal/min
at 7 bar 100 psi	
Cavity	Consult factory




15


4

22.5

6



DIMENSIONS



L = 1/4 BSP