

Flow Control Valves Catalog


Velocity Fuse BC 10

OPERATION

SPECIFICATIONS

This is an in-line flow limiter that closes and then provides non-compensated restricted flow when the specified flow setting is exceeded. The valve provides free reverse flow when operated in the opposite direction.

Schematic




Specifications


	210 bar 3000 psi
Pressure rating	
Rated Free Flow	60 l/min 16 US gal/min
at 7 bar 100 psi	
Cavity	Consult factory

Theoretical performance


Pressure drop from P⇒C according to Adjustment H 26 cSt [121 SUS] hyd.oil at 50°C [122 °F]



Values for adjustment H are guideline only, being conditioned by a variety of factors (oil temperature and viscosity, volume and flexibility of circuits).



DIMENSIONS



ORDERING INFORMATION

