


Cartridge Valves Technical Information Motor Mount HICs MM-DS-00-SVP10-NCR

OPERATION

This is a bypass solenoid HIC with drain that mounts to DH motors with manifold mount porting. When energized, the valve connects ports A and B. Drain connects to port A.

Schematic




P104 750

SPECIFICATIONS

Theoretical performance

Pressure drop




Specifications

Rated pressure	210 bar [3045 psi]
Rated flow at 7 bar	80 l/min [21 US gal/min]
[102 psi]	
Leakage	6 drops/min @ at rated
	pressure
Weight	1.47 kg [3.24 lb]
Cartridge	SVP10-NCR
Shuttle/drain port	#4 SAE (1/4 BSP)
Service mount kit	11023865
Motor	DS

DIMENSIONS

Cross-sectional view

mm [in]



ORDERING INFORMATION

